

QE12HR-H-MB-D0

Pyroelectric detector for laser energy measurement up to 0.85 J.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

 $0.7 \, \mu J$ for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read more.

HIGH REPETITION RATE OPTIONS

- QE12HR-MB: 1 000 Hz
- QE12HR-MT: 10 000 Hz

TEST TARGET INCLUDED

With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-D-233

SPECIFICATIONS

MEASUREMENT CAPABILITIES

Spectral range ¹	0.193 - 20 μm
Typical rise time	70 µs
Repeatability	<0.5%
Maximum repetition frequency ²	1000 Hz
Maximum measurable energy ³	0.85 J
Noise equivalent energy ⁴	1.4 μJ
Maximum pulse width	40 µs
Energy calibration uncertainty	±3 %

- 1. For the calibrated spectral range, see the user manual.
- $2. \ May be limited by the display or PC interface. Please refer to the corresponding user manual.\\$
- ${\it 3. At 1064}\ nm, {\it 7}\ ns, {\it 10}\ Hz.\ Increasing\ pulse\ width\ increases\ maximum\ measurable\ energy.$
- ${\it 4.}\ {\it Nominal value}. Actual value depends on electrical noise in the measurement system.$

DAMAGE THRESHOLDS

27 11 11 12 11 11 12 11 12 12 1	
Maximum average power density ¹	10 W/cm ²
Maximum energy density ²	0.6 J/cm ²
Maximum power	5 W

- 1. May vary with wavelength and average power.
- 2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS

Cooling	Convection (heatsink)
Aperture width	12 mm
Aperture height	12 mm
Absorber	МВ
Dimensions	36H x 36W x 33D mm

Weight 0.12 kg

ORDERING INFORMATION	
QE12HR-H-MB-D0	203895
QE12HR-H-MB-INT-D0	203903
QE12HR-H-MB-INE-D0	
QE12HR-H-MB-IDR-D0	205363

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?



Find your local sales representative at gentec-eo.com/contact-us