

QE25LP-H-MB-D0

최대 3.75 J의 레이저 에너지 계측용 초전기 검출기.



제품군 주요 특징

- MODULAR CONCEPT**
Increase the power capability of your detector: 2 different cooling modules
- LOW NOISE LEVEL**
2 μ J for the MB coating
- QED ATTENUATOR AVAILABLE**
Measure higher energy levels. Available with optional calibration, all wavelengths between 532 and 1064 nm, or single wavelength [Read more](#).
- HIGH REPETITION RATE OPTIONS**
 - QE25HR-MB: 1 000 Hz
 - QE25HR-MT: 10 000 Hz
- TEST TARGET INCLUDED**
With the MB models
- SMART INTERFACE**
Containing all the calibration data
- 호환 스탠드**
[STAND-D-233](#)

사양

계측 성능	
스펙트럼 범위 ¹	0.193 - 20 μ m
일반 상승 시간	550 μ s
반복성	<0.5%
최대 반복 주파수 ²	300 Hz
최대 계측가능 에너지 ³	3.75 J
등가노이즈에너지 ⁴	4 μ J
최대 펄스폭	400 μ s
에너지 교정 불확정성	$\pm$ 3 %
1. 교정된 스펙트럼 범위는 사용설명서를 참조하십시오. 2. 디스플레이 또는 PC 인터페이스로 제한될 수 있습니다. 해당하는 사용자 매뉴얼을 참조하십시오. 3. 1064nm, 7ns, 10Hz. 4. 액면 값. 실제 값은 측정 시스템의 전기적 노이즈에 따라 달라집니다.	
손상 한계	
최대 평균 파워 밀도 ¹	10 W/cm ²
최대 에너지 밀도 ²	0.6 J/cm ²
최대 파워	10 W
1. May vary with wavelength and average power. 2. 1064nm, 7ns, 10Hz. May vary with wavelength and pulse width.	
물리적 특성	
냉각	대류(방열판)
구경 너비	25 mm
구경 높이	25 mm
업소버	MB
치수	50H x 50W x 53D mm
중량	0.193 kg

주문 정보	
QE25LP-H-MB-D0	200457
QE25LP-H-MB-INT-D0	202383
QE25LP-H-MB-IDR-D0	203262
QE25LP-H-MB-INE-D0	

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

이 제품에 관심이 있으십니까?

견적받기

gentec-eo.com/ko/contact-us에서 현지 영업 담당자를 찾으십시오.