

# QE65LP-H-MB-D0

Pyroelectric detector for laser energy measurement up to 50 J.



# PRODUCT FAMILY KEY FEATURES

# MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

# LARGE APERTURE

Effective aperture of 65 x 65 mm

#### **QED ATTENUATOR AVAILABLE**

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read more.

# LOW NOISE LEVEL

10 µJ for the MB coating

# **TEST TARGET INCLUDED**

With the MB models

#### **SMART INTERFACE**

Containing all the calibration data

# **COMPATIBLE STAND**

STAND-D-443

# **SPECIFICATIONS**

MEASUREMENT CAPABILITIES	
Spectral range <sup>1</sup>	0.193 - 20 μm
Typical rise time	1 ms
Repeatability	<0.5%
Maximum repetition frequency	100 Hz
Maximum measurable energy <sup>2</sup>	50 J
Noise equivalent energy <sup>3</sup>	10 μ3
Maximum pulse width	0.7 ms
Energy calibration uncertainty	±3 %
1 For the calibrated spectral range, see the user manual	

- 1. For the calibrated spectral range, see the user manual.
- 2. At 1064 nm, 150  $\mu$ s, single-shot. Increasing pulse width increases maximum measurable energy.
- 3. Nominal value. Actual value depends on electrical noise in the measurement system.

# DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	10 W/cm <sup>2</sup>
Maximum energy density <sup>2</sup>	0.6 J/cm <sup>2</sup>
Maximum power	40 W

- 1. May vary with wavelength and average power.
- 2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

# PHYSICAL CHARACTERISTICS

Cooling	Convection (heatsink)
Aperture width	65 mm
Aperture height	65 mm
Absorber	МВ
Dimensions	92H x 92W x 99D mm
Weight	0.9 kg

# ORDERING INFORMATION

QE65LP-H-MB-D0 201253

QE65LP-H-MB-IDR-D0	203292
QE65LP-H-MB-INE-D0	
QE65LP-H-MB-INT-D0	202762

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

# **INTERESTED IN THIS PRODUCT?**

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us