

## QE95LP-S-MB-D0

Pyroelectric detector for laser energy measurement up to 35 J.



### KEY FEATURES

#### MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

#### EXTRA LARGE APERTURE

Effective aperture of 95 mm  $\varnothing$

#### QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. [Read more.](#)

#### LOW NOISE LEVEL

15  $\mu$ J for the MB coating

#### TEST TARGET INCLUDED

With the MB models

#### SMART INTERFACE

Containing all the calibration data

#### COMPATIBLE STAND

[STAND-D-233](#)

## SPECIFICATIONS

### MEASUREMENT CAPABILITIES

Spectral range <sup>1</sup>	0.193 - 20 $\mu$ m
Typical rise time	2 ms
Repeatability	<0.5%
Maximum repetition frequency	40 Hz
Typical energy sensitivity	2 V/J
Maximum measurable energy <sup>2</sup>	35 J
Noise equivalent energy <sup>3</sup>	15 $\mu$ J
Maximum pulse width	1.5 ms
Energy calibration uncertainty	$\pm$ 3 %

1. For the calibrated spectral range, see the user manual.

2. At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.

3. Nominal value. Actual value depends on electrical noise in the measurement system.

### DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	10 W/cm <sup>2</sup>
Maximum energy density <sup>2</sup>	0.6 J/cm <sup>2</sup>
Maximum power	20 W

1. At 1064 nm, 7 ns, 10 Hz.

2. At 1064 nm, 7 ns, 10 Hz.

### PHYSICAL CHARACTERISTICS

Aperture diameter	95 mm
Absorber	MB
Dimensions	122H x 122W x 20D mm
Weight	0.78 kg

### ORDERING INFORMATIONS

QE95LP-S-MB-D0	201307
QE95LP-S-MB-INE-D0	

## INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at [gentec-eo.com/contact-us](https://gentec-eo.com/contact-us)