

# HP60A-15KW-GD-QBH-MET-D0

High power detector for laser power measurement up to 15 000 W. Includes QB/QBH fiber adaptor.



# PRODUCT FAMILY KEY FEATURES

#### HIGH POWER HANDLING

Handles up to 30 kW of continuous power with our standard models. Custom models are available for higher powers (See SUPER HP).

#### STABLE READING

Less sensitive to variations in water cooling temperature than any other high-power water-cooled meter on the market

### LARGE APERTURE

Our standard HP models (4KW, 12KW, 15KW and 30KW) have a very large effective aperture of up to 280 mm to accommodate even the largest laser beams. Larger apertures with various shapes are available upon request (See SUPER HP).

### AVAILABLE WITH YAG AND CO2 CALIBRATION

All HP Models can be calibrated at YAG and  $\rm CO_2$  wavelengths with a calibration uncertainty of +/- 5%

#### DIRECT USB CONNECTION TO A PC

Each head comes with both a DB-15 connector (for use with a Gentec-EO monitor) and a USB2.0 output for direct connection to a PC.

### AWARD-WINNING TECHNOLOGY

The HP-BLU series wireless detectors for high-power lasers were recognized among the best by an esteemed and experienced panel of judges from the optics and photonics community at the 2020 Laser Focus World Innovators Awards.



# **SPECIFICATIONS**

# **MEASUREMENT CAPABILITIES**

Maximum average power (continuous)	15000 W
Minimum average power <sup>1</sup>	500 W
Noise equivalent power <sup>2</sup>	15 W
Spectral range	0.8 - 12 μm
Typical rise time	15 s
Power calibration uncertainty	±5 %
Repeatability	±2 %
Back reflections	1 - 2 %
Linearity with power	±2 %
Linearity vs beam diameter	±2.5 %
Linearity vs beam position <sup>3</sup>	±4 %

- 1. For lower powers, call your Gentec-EO representative.
- 2. Nominal value. Actual value depends on electrical noise in the measurement system.
- 3. For a beam size of 20% of the aperture area, moved across 80% of the aperture area.

# WATER REQUIREMENTS

Required cooling flow<sup>1</sup> (8 - 10) LPM < ±1 LPM/min

Temperature range 15 − 25 °C

Rate of temperature change	< ±3°C/min	
Maximum water pressure	413 kPa (60 psi)	
1. Contact Gentec-EO for clean deionized water cooling module option.		
DAMAGE THRESHOLDS		
Maximum average power density <sup>1</sup>	80 kW/cm²	
1. At 1064 nm, 1.07-1.08 $\mu m$ and 10.6 $\mu m$ , 500 W CW. Refer to user manual for damage threshold at	other powers. May vary with wavelength and average power.	
CONTROLLER AND GUI SPECIFICATIONS		
Data display	Real time, scope, needle, averaging, histogram and statistics	
Analog output <sup>1</sup>	0-2 Volts	
Serial commands via	USB	
External power supply <sup>2</sup>	Through USB or Gentec-EO displays & PC interfaces	
Display type	None	
1. 12 V maximum output signal available upon request. 2. A USB power adaptor will be necessary if the HP is used with a DB-15 extension cable.		
PHYSICAL CHARACTERISTICS		
Cooling	Water	
Aperture diameter	70 mm	
Absorber	GD	
Dimensions	153H x 153W x 386D mm	
Weight	16 kg	
ORDERING INFORMATION		
HP60A-15KW-GD-QBH-MET-D0	205558M	
HP60A-15KW-GD-QBH-MET-BLU-D0	TBD	

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

# **INTERESTED IN THIS PRODUCT?**

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us