

QE50LP-H-MB-D0

Pyroelectric detector for laser energy measurement up to 15 J.



KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

10 μ J for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. [Read more.](#)

HIGH REPETITION RATE OPTIONS

- QE-MB: 200 Hz (standard)
- QE-MB: 500 Hz (upon request)
- QE-MT: 4 000 Hz (standard)

TEST TARGET INCLUDED

With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

[STAND-D-233](#)

SPECIFICATIONS

MEASUREMENT CAPABILITIES

Spectral range ¹	0.193 - 20 μ m
Typical rise time	900 μ s
Repeatability	<0.5%
Maximum repetition frequency	200 Hz
Typical energy sensitivity	3 V/J
Maximum measurable energy ²	15 J
Noise equivalent energy ³	10 μ J
Maximum pulse width	675 μ s
Energy calibration uncertainty	\pm 3 %

1. For the calibrated spectral range, see the user manual.

2. At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.

3. Nominal value. Actual value depends on electrical noise in the measurement system.

DAMAGE THRESHOLDS

Maximum average power density ¹	10 W/cm ²
Maximum energy density ²	0.6 J/cm ²
Maximum power	20 W

1. At 1064 nm, 7 ns, 10 Hz.

2. At 1064 nm, 7 ns, 10 Hz.

PHYSICAL CHARACTERISTICS

Aperture width	50 mm
Aperture height	50 mm
Absorber	MB
Dimensions	75H x 75W x 44D mm

ORDERING INFORMATION

QE50LP-H-MB-D0	200481
QE50LP-H-MB-INT-D0	202746
QE50LP-H-MB-IDR-D0	203276
QE50LP-H-MB-INE-D0	

INTERESTED IN THIS PRODUCT?

[GET A QUOTE](#)

Find your local sales representative at gentec-eo.com/contact-us