

### UP50M-50W-W9-D0

Thermal detector for laser power measurement up to 50 W.



#### PRODUCT FAMILY KEY FEATURES

#### THIS PRODUCT HAS BEEN SUPERSEDED. CHECK THIS PAGE FOR THE NEW PRODUCT.

+0.5 %

#### MODULAR CONCEPT

Increase the power capability of your detector: 4 different cooling modules

#### VERY HIGH DAMAGE THRESHOLD

100 kW/cm<sup>2</sup> in average power density

#### **VERY LARGE APERTURE**

50 mm effective aperture diameter, perfect for the largest beams

#### HIGHEST ENERGY READINGS IN THE SERIES

Measure single shot energy up to 500  ${\tt J}$ 

#### **SMART INTERFACE**

Containing all the calibration data

#### **COMPATIBLE STAND**

STAND-S-443

## **SPECIFICATIONS**

Maximum average power (continuous) <sup>1</sup>	50 W
Maximum average power (1 minute) <sup>2</sup>	85 W
Noise equivalent power <sup>3</sup>	5 mW
Spectral range <sup>4</sup>	0.193 - 10 µm
Typical rise time <sup>5</sup>	3.5 s
Power calibration uncertainty <sup>6</sup>	±2.5 %

- 1. Minimum cooling flow 1 liters/min, water temperature  $\leq$  22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module
- 2. Minimum cooling flow 1 liters/min, water temperature  $\leq$  22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module
- 3. Nominal value, actual value depends on electrical noise in the measurement system.
- 4. For the calibrated spectral range, see the user manual.
- 5. With anticipation.

Repeatability

6. Including linearity with power.

MEASUREMENT CAPABILITIES

### MEASUREMENT CAPABILITIES (ENERGY MODE)

MERIOREMENT ON ANDIENTES (ENERGY MODE)	
Maximum measurable energy <sup>1</sup>	500 J
Noise equivalent energy <sup>2</sup>	0.25 J
Minimum repetition period	11.1 s
Maximum pulse width	467 ms
Energy calibration uncertainty <sup>3</sup>	±5 %

- 1. For 360 µs pulses. Higher pulse energy possible for long pulses (ms), less for short pulses (ns).
- 2. Nominal value, actual value depends on electrical noise in the measurement system.
- 3. When single-shot energy calibration is purchased

#### DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	100 kW/cm	2

1.1 J/cm<sup>2</sup> Maximum energy density<sup>2</sup>

- 1. At 1064 nm, 10 W CW. May vary with wavelength and average power.
- 2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS	
Cooling	Water
Aperture diameter	50 mm
Absorber	W
Dimensions	119H x 89W x 46D mm
Weight	0.81 kg
ORDERING INFORMATION	
UP50M-50W-W9-D0	201886
UP50M-50W-W9-IDR-D0	203367
UP50M-50W-W9-BLU-D0	203682
IIPS0M-50W-W9-INT-D0	203065

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

# **INTERESTED IN THIS PRODUCT?**



Find your local sales representative at gentec-eo.com/contact-us