

M6-6-SI

Weight

ORDERING INFORMATION

Integrating sphere detector for laser energy measurement up to 200 μJ .



KEY FEATURES

UP TO 200 KHZ PULSE-TO-PULSE

Measure every pulse, with no sampling, at high rep rates, up to 200 kHz

CAPTURE AND STORE UP TO 4 MILLION PULSES

Store 40 seconds of data at 100 kHz

TRACK MISSING PULSES AND PULSES BELOW THRESHOLD

Know how many pulses were missed or that didn't make the energy threshold with this unique pulse feature $\,$

SEVERAL HEADS TO CHOOSE FROM

Silicon, InGaAs and pyroelectric heads for a broad wavelength and energy range

ANALOG MODULE AVAILABLE

Use our fast M6 detectors with the APM and an oscilloscope for fast analog energy measurements

FULL-SPEED USB 2.0 CONNECTION

Ensures high data rate transfer and fast operation

USER-FRIENDLY SOFTWARE WITH MANY DIAGNOSTIC FEATURES

0.15 kg

- Live mode, strip chart, histogram and statistics displays
- FFT display of pulse energy data for temporal diagnostics
- Life test mode to automate laser testing

COMPATIBLE STAND

STAND-D-233

SPECIFICATIONS

MEASUREMENT CAPABILITIES	
Spectral range	0.35 - 1.1 μm
Typical rise time	150 ns
Repeatability	±1 %
Maximum repetition frequency	200000 Hz
Maximum measurable energy ^l	200 μJ
Noise equivalent energy	2 nJ
Maximum pulse width	100 ns
Energy calibration uncertainty	±4 %
1. Maximum pulse energy reading will vary with wavelength and probe voltage responsivity. For more details, please read Application Note 121D-2 eo.com	01932 and contact us at info@gentec-
DAMAGE THRESHOLDS	
Maximum power	5 W
PHYSICAL CHARACTERISTICS	
Aperture diameter	6 mm
Absorber	Si
Dimensions	38.1 Ø x 58.4D mm

M6-6-Si 202115

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us