

## UP55M-500W-H12-D0

Thermal detector for laser power measurement up to 500 W.



### KEY FEATURES

#### MODULAR CONCEPT

Increase the power capability of your detector: 4 different cooling modules

#### HIGH PERFORMANCE

- Fast Rise Time (2 sec)
- High Damage Threshold (45 kW/cm<sup>2</sup>)

#### COMPACT DESIGN

Only 32 mm thick (40S model)

#### ENERGY MODE

Measure single shot energy up to 200 J

#### SMART INTERFACE

Containing all the calibration data

#### COMPATIBLE STAND

[STAND-S-443](#)

## SPECIFICATIONS

### MEASUREMENT CAPABILITIES

Maximum average power (continuous) <sup>1</sup>	500 W
Maximum average power (1 minute) <sup>2</sup>	500 W
Noise equivalent power <sup>3</sup>	15 mW
Spectral range <sup>4</sup>	0.193 - 20 μm
Typical rise time <sup>5</sup>	2 sec
Typical power sensitivity <sup>6</sup>	0.06 mV/W
Power calibration uncertainty <sup>7</sup>	±2.5 %
Repeatability	±0.5 %

1. Minimum cooling flow 1.5 liters/min, water temperature ≤ 22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module option.

2. Minimum cooling flow 1.5 liters/min, water temperature ≤ 22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module option.

3. Nominal value, actual value depends on electrical noise in the measurement system.

4. For the calibrated spectral range, see the user manual.

5. With anticipation.

6. Into 100 kΩ load. Maximum output voltage = sensitivity x maximum power.

7. Including linearity with power.

### MEASUREMENT CAPABILITIES (ENERGY MODE)

Typical energy sensitivity	0.015 mV/J
Maximum measurable energy <sup>1</sup>	200 J
Noise equivalent energy <sup>2</sup>	0.25 J
Minimum repetition period	12 s
Maximum pulse width	430 ms
Energy calibration uncertainty <sup>3</sup>	±5 %

1. For 360 μs pulses. Higher pulse energy possible for long pulses (ms), less for short pulses (ns).

2. Nominal value, actual value depends on electrical noise in the measurement system.

3. When single-shot energy calibration is purchased

### DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	45 kW/cm <sup>2</sup>
--	-----------------------

Maximum energy density<sup>2</sup>

1 J/cm<sup>2</sup>

1. At 1064 nm, 10 W CW.
2. At 1064 nm, 7 ns, 10 Hz.

## PHYSICAL CHARACTERISTICS

Aperture diameter	55 mm
Absorber	H12
Dimensions	89H x 89W x 40D mm
Weight	0.81 kg

## ORDERING INFORMATION

UP55M-500W-H12-D0	201882
UP55M-500W-H12-INT-D0	203069
UP55M-500W-H12-IDR-D0	203377
UP55M-500W-H12-BLU-D0	203691

## INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at [gentec-eo.com/contact-us](http://gentec-eo.com/contact-us)