

## NDSET-FOCUS-6

Set of 6 ND filters in SM2 holders: ND0.5-FOCUS, ND1.0-FOCUS, ND2.0-FOCUS, ND3.0-FOCUS, ND4.0-FOCUS, ND5.0-FOCUS.

### PRODUCT FAMILY KEY FEATURES

#### MANAGE THE LASER POWER

CMOS sensors have low saturation levels as well as low damage thresholds. It is thus very important that you control your laser power to get the best measurement possible and avoid damaging the BEAMAGE camera.

#### STACK AND ATTENUATE AS MUCH AS YOU NEED

These filters reduce the intensity of all wavelengths without affecting the wavefront of the beam or distorting the image. Many filters can be stacked directly on each other.



## SPECIFICATIONS

### MEASUREMENT CAPABILITIES

Spectral range	400 - 1595 nm
Transmittance	See ND0.5-FOCUS, ND1.0-FOCUS, ND2.0-FOCUS, ND3.0-FOCUS, ND4.0-FOCUS, and ND5.0-FOCUS.
Equivalent attenuation	See ND0.5-FOCUS, ND1.0-FOCUS, ND2.0-FOCUS, ND3.0-FOCUS, ND4.0-FOCUS, and ND5.0-FOCUS.
Parallelism	< 3 arcmin
Optical density tolerance	± 5%
Transmitted wavefront error	< λ/10 @ 633 nm
Surface quality	40-20 Scratch-Dig

### DAMAGE THRESHOLDS

Maximum average power density	100 W/cm <sup>2</sup>
Maximum energy density	3 J/cm <sup>2</sup>
Maximum power	1 W

### PHYSICAL CHARACTERISTICS

Aperture diameter	48 mm
Dimensions	30.5Ø x 11.4D mm
Weight	0.2 kg
Mounting thread	SM2
Clear aperture	90% of area
Dimensional tolerance	+0.0/-0.25 mm
Substrate	See ND0.5-FOCUS, ND1.0-FOCUS, ND2.0-FOCUS, ND3.0-FOCUS, ND4.0-FOCUS, and ND5.0-FOCUS.

### ORDERING INFORMATION

NDSET-FOCUS-6	206010
---------------	--------

## INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at [gentec-eo.com/contact-us](https://gentec-eo.com/contact-us)