# gentec-ۥ)

### UD19-200-H9

Uncalibrated thermal disk sensor for laser power measurement up to 200 W.



### **KEY FEATURES**

#### **DESIGNED FOR INTEGRATION**

With a broad bandwidth and high power densities

#### **VERY THIN PROFILES**

Starting at only 2 mm in thickness

#### VARIOUS APERTURE SIZES

Choose your aperture from 10 mm to 55 mm.

100 kΩ

0 27 001/7

### **2 LEVELS OF INTEGRATION**

- Disk alone
- Disk + PCB

## **SPECIFICATIONS**

Maximum average power	200 W
Maximum average power (fan-cooled)	110 W
Noise equivalent power	3 mW
Spectral range	0.19 - 20 µm
Typical rise time <sup>1</sup>	4.5 sec
Typical power sensitivity <sup>2</sup>	0.23 mV/W

### Maximum divergence

Recommended load impedance

1. These characteristics depend on the thermal management and electronics provided by the user. Packaging, cooling and electronics similar to our UP series detectors will provide similar performances. See UP series specifications sheets for more details. Actual performance depends on the tradeoffs in a user's design. It may be possible to enhance some performance parameters at the expense of others.

2. Without anticipation algorithm or circuitry.

MEASUREMENT CAPABILITIES

### MEASUREMENT CAPABILITIES (ENERGY MODE)

Typical energy sensitivity	0.23 1110/3
Maximum measurable energy <sup>1</sup>	25 J
Noise equivalent energy	60 mJ

1. For 360 µs pulses. Higher pulse energy possible for long pulses (ms), less for short pulses (ns).

### DAMAGE THRESHOLDS

Maximum average power density	45 kW/cm²
Maximum energy density <sup>1</sup>	1 J/cm²

1. At 1064 nm, 7 ns, 10 Hz.

### PHYSICAL CHARACTERISTICS

	perture diameter	is min
Al	bsorber	H9

Dimensions 44Ø x 3D mm

Weight 0.007 kg

ORDERING INFORMATIONS

UD19-200-H9 200576

# **INTERESTED IN THIS PRODUCT?**

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us