

## QE12SP-H-MT-D0

Pyroelectric detector for laser energy measurement up to 0.70 J.



#### PRODUCT FAMILY KEY FEATURES

#### MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

0.7 µJ for the MB coating

#### **QED ATTENUATOR AVAILABLE**

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read more.

#### HIGH REPETITION RATE OPTIONS

- QE12HR-MB: 1 000 Hz
- QE12HR-MT: 10 000 Hz

#### TEST TARGET INCLUDED

With the MB models

#### SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-D-233

### **SPECIFICATIONS**

#### MEASUREMENT CAPABILITIES

Spectral range <sup>1</sup>	0.193 - 20 µm
Typical rise time	20 µs
Repeatability	<0.5%
Maximum repetition frequency <sup>2</sup>	6000 Hz
Maximum measurable energy <sup>3</sup>	0.7 J
Noise equivalent energy <sup>4</sup>	Cμ 8.0
Maximum pulse width	10 µs
Energy calibration uncertainty	±3 %

1. For the calibrated spectral range, see the user manual.

2. May be limited by the display or PC interface. Please refer to the corresponding user manual.

3. At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.

4. Nominal value. Actual value depends on electrical noise in the measurement system.

### DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	10 W/cm <sup>2</sup>
Maximum energy density <sup>2</sup>	0.5 J/cm²
Maximum power	5 W

1. May vary with wavelength and average power.

2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

#### PHYSICAL CHARACTERISTICS

Cooling	Convection (heatsink)
Aperture width	12 mm
Aperture height	12 mm
Absorber	МТ
Dimensions	36H x 36W x 33D mm

Weight

QE12SP-H-MT-D0

QE12SP-H-MT-INT-D0

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

# INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us