

QE50LP-S-MB-D0

최대 15 J의 레이저 에너지 계측용 초전기 검출기.



제품군 주요 특징

- MODULAR CONCEPT**
Increase the power capability of your detector: 2 different cooling modules
- LOW NOISE LEVEL**
10 µJ for the MB coating
- QED ATTENUATOR AVAILABLE**
Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. [Read more.](#)
- HIGH REPETITION RATE OPTIONS**
 - QE-MB: 200 Hz (standard)
 - QE-MB: 500 Hz (upon request)
 - QE-MT: 4 000 Hz (standard)
- TEST TARGET INCLUDED**
With the MB models
- SMART INTERFACE**
Containing all the calibration data
- 호환 스탠드**
[STAND-D-233](#)



사양

계측 성능	
스펙트럼 범위 ¹	0.193 - 20 µm
일반 상승 시간	900 µs
반복성	<0.5%
최대 반복 주파수	200 Hz
최대 계측가능 에너지 ²	15 J
등가노이즈에너지 ³	10 µJ
최대 펄스폭	675 µs
에너지 교정 불확정성	±3 %
1. 교정된 스펙트럼 범위는 사용설명서를 참조하십시오. 2. 1064nm, 7ns, 10Hz. 3. 액면 값. 실제 값은 측정 시스템의 전기적 노이즈에 따라 달라집니다.	
손상 한계	
최대 평균 파워 밀도 ¹	10 W/cm²
최대 에너지 밀도 ²	0.6 J/cm²
최대 파워	10 W
1. May vary with wavelength and average power. 2. 1064nm, 7ns, 10Hz. May vary with wavelength and pulse width.	
물리적 특성	
냉각	대류
구경 너비	50 mm
구경 높이	50 mm
업소버	MB
치수	75H x 75W x 15D mm

중량	0.21 kg
주문 정보	
QE50LP-S-MB-D0	200479
QE50LP-S-MB-INE-D0	
QE50LP-S-MB-INT-D0	202750
QE50LP-S-MB-IDR-D0	203280

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

이 제품에 관심이 있으십니까?

견적받기

gentec-eo.com/ko/contact-us에서 현지 영업 담당자를 찾으십시오.