

UP19K-15S-H5-D0

Thermal detector for laser power measurement up to 15 W.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 5 different cooling modules

HIGH PERFORMANCE

- Fast rise time (0.6 sec)
- High damage threshold (36 kW/cm²)

COMPACT DESIGN

Only 20.6 mm thick (15S model)

ENERGY MODE

Measure single shot energy up to 15 ${\tt J}$

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-S-233

SPECIFICATIONS

MEASUREMENT CAPABILITIES	
Maximum average power (continuous)	15 W
Maximum average power (1 minute)	30 W
Noise equivalent power ¹	1 mW
Spectral range ²	0.193 - 20 μm
Typical rise time ³	0.6 s
Power calibration uncertainty ⁴	±2.5 %
Repeatability	±0.5 %

- 1. Nominal value, actual value depends on electrical noise in the measurement system.
- 2. For the calibrated spectral range, see the user manual.
- 3. With anticipation.
- 4. Including linearity with power.

MEASUREMENT CAPABILITIES (ENERGY MODE)

MEASUREMENT CAPABILITIES (ENERGY MODE)	
Maximum measurable energy ¹	15 J
Noise equivalent energy ²	0.02 J
Minimum repetition period	4 s
Maximum pulse width	88 ms
Energy calibration uncertainty ³	±5 %

- 1. For 360 μs pulses. Higher pulse energy possible for long pulses (ms), less for short pulses (ns).
- 2. Nominal value, actual value depends on electrical noise in the measurement system.
- 3. When single-shot energy calibration is purchased

DAMAGE THRESHOLDS

Maximum average power density¹ 36 kW/cm²
Maximum energy density² 11J/cm²

- 1. At 1064 nm, 10 W CW. May vary with wavelength and average power.
- 2. At 1064 nm, 7 ns, 10 Hz. Damage thresholds vary with pulse width. Use our Product Finder or contact Gentec-EO to know about damage thresholds for different pulse widths.

PHYSICAL CHARACTERISTICS

Cooling

Aperture diameter	19 mm
Absorber	H5
Dimensions	50H x 50W x 20.6D mm
Weight	0.16 kg
ORDERING INFORMATION	
UP19K-15S-H5-D0	200142
UP19K-15S-H5-BLU-D0	203433
UP19K-15S-H5-IDR-D0	203337
UP19K-15S-H5-INT-D0	202617

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us